

Silopren™ LSR 2650

Description

Silopren LSR 2650 is a two-component liquid silicone rubber for injection molding processes. In comparison to Silopren LSR 2050, Silopren LSR 2650 shows a lower viscosity, improved tear resistance and a higher reactivity. Therefore, it is also possible to reduce the vulcanization temperature while maintaining a standard crosslinking rate. The increased reactivity does not affect the properties of the vulcanizate.

Key Features and Benefits

Vulcanizates of Silopren LSR 2650 are typically distinguished by the following properties:

- High reactivity, lower viscosity, shorter cycle time
- Excellent thermal stability
- High stability and flexibility at low temperatures
- Good rubber-like properties, high tear resistance
- Long service life at dynamic stress
- High stability to ozone and ultraviolet light
- Outstanding resistance to aging
- Excellent dielectric behavior over a wide range of temperatures
- Easily pigmentable with LSR color pastes
- KTW approved

Typical Physical Properties

Typical Properties of the Rubber:	ical Properties of the Rubber:				
		A-part	B-part		
Appearance		Translucent	Translucent		
Viscosity in Pa•s gamma= 10 s ⁻¹ at 20°C	DIN 53018	450	450		

The pot-life of the mixture of the two components (closed vessel) at 20°C is usually three days. Increased temperatures reduce the pot-life.

Typical Properties of the Vulcanizate:				
Mixing Ratio of Components $A : B = 1$				
: 1.				
Vulcanization: 10 min. 175°C + 4 hrs				
200°C post-cure				

Density	DIN 53 479 A	g/cm ³	1.12
Shore A Hardness	DIN 53 505		52
Tensile Strength	DIN 53 504 S2	N/mm ²	10.0
Elongation at Break	DIN 53 504 S2	%	550
Compression Set	DIN 53 517 (22 h at 175°C)	%	25

Typical data are average data and actual values may vary.

Typical data shall not be used as product specifications.

Potential Applications

Because of its outstanding properties, Silopren LSR 2650 is an excellent candidate to consider for the following elastomeric articles:

- Sealing elements
- O-rings
- Stoppers
- Diaphragms
- Keypads
- Pacifiers
- Baby teats
- Vibration dampers
- Air vent flaps
- Switch cover
- Breast shields
- Nose pads
- Pressure cookers parts
- Spark plug boots
- Cable connectors

Processing Recommendations

Ready-to-use mixtures (of the components A and B) are fed directly to the injection molding machine from the original containers by means of a metering and mixing unit. The mixture, consisting of the two components in the ratio 1:1, is injected into the heated mold. At mold temperatures of 140 - 200°C, the addition-crosslinking silicone rubber typically vulcanizes without any dissociation products within a few seconds. High curing speed and easy demolding can help enable the fully automated production of a large number of articles in short cycle times.

Regulatory Compilance

- Compositionally compliant with the requirements of 21 CFR 177.2600 Rubber articles intended for repeated use and have been found, through testing of a representative sample, to meet the extractives limitations in 21 CFR 177.2600(e) and/or (f)⁽¹⁾
- The ingredients are listed in the BfR recommendation XV "Silicones" (3)
- KTW approved
- In compliance with the requirements of the DVGW Working sheet W 270
- WRAS approved product (BS 6920)
- (1) It is the responsibility of the user to determine that the final product complies with the extractive limitations and other requirements of 21 CFR 177.2600 under their specific manufacturing procedures.
- (2) Please contact Product Stewardship and Regulatory Group for details
- (3) Producer of the final article needs to test and confirm that the final product meets the extraction limits of BfR XV or corresponding EU legislation

Containers

Silopren LSR 2650 is available in 20 kg pails and 200 kg drums.

Patent Status

Nothing contained herein shall be construed to imply the nonexistence of any relevant patents or to constitute the permission, inducement or recommendation to practice any invention covered by any patent, without authority from the owner of the patent.

Product Safety, Handling and Storage

Customers should review the latest Safety Data Sheet (SDS) and label for product safety information, safe handling instructions, personal protective equipment if

necessary, emergency service contact information, and any special storage conditions required for safety. Momentive Performance Materials (MPM) maintains an around-the-clock emergency service for its products. SDS are available at www.momentive.com or, upon request, from any MPM representative. For product storage and handling procedures to maintain the product quality within our stated specifications, please review Certificates of Analysis, which are available in the Order Center. Use of other materials in conjunction with MPM products (for example, primers) may require additional precautions. Please review and follow the safety information provided by the manufacturer of such other materials.

Limitations

Customers must evaluate Momentive Performance Materials products and make their own determination as to fitness of use in their particular applications.

Contact Information

Fmail

commercial services@momentive.com

Telephone			
Americas	Latin America	EMEAI- Europe, Middle East, Africa & India	ASIA PACIFIC
+1 800 295 2392	Brazil	Europe	China
Toll free*	+55 11 4534 9650	+390510924300	800 820 0202
+704 805 6946	Direct Number	Direct number	Toll free
Direct Number			+86 21 3860 4892
			Direct number
*All American	Mexico	India, Middle East &	Japan
countries	+52 55 2169 7670	Africa	+81 3 5544 3111
	Direct Number	+ 91 44 71212207	Direct number
		Direct number*	
		*All Middle Eastern	Korea
		countries, Africa, India,	+82 2 6201 4600

For literature and technical assistance, visit our website at: www.momentive.com

DISCLAIMER:

THE MATERIALS, PRODUCTS AND SERVICES OF MOMENTIVE PERFORMANCE MATERIALS INC. AND ITS SUBSIDIARIES AND AFFILIATES (COLLECTIVELY "SUPPLIER"), ARE SOLD SUBJECT TO SUPPLIER'S STANDARD CONDITIONS OF SALE, WHICH ARE INCLUDED IN THE APPLICABLE DISTRIBUTOR OR OTHER SALES AGREEMENT, PRINTED ON THE BACK OF ORDER ACKNOWLEDGMENTS AND INVOICES, AND AVAILABLE UPON REQUEST. ALTHOUGH ANY INFORMATION. RECOMMENDATIONS. OR ADVICE CONTAINED HEREIN IS GIVEN IN GOOD FAITH, SUPPLIER MAKES NO WARRANTY OR GUARANTEE, EXPRESS OR IMPLIED, (i) THAT THE RESULTS DESCRIBED HEREIN WILL BE OBTAINED UNDER END-USE CONDITIONS, OR (ii) AS TO THE EFFECTIVENESS OR SAFETY OF ANY DESIGN INCORPORATING ITS PRODUCTS, MATERIALS, SERVICES, RECOMMENDATIONS OR ADVICE. EXCEPT AS PROVIDED IN SUPPLIER'S STANDARD CONDITIONS OF SALE. SUPPLIER AND ITS REPRESENTATIVES SHALL IN NO EVENT BE RESPONSIBLE FOR ANY LOSS RESULTING FROM ANY USE OF ITS MATERIALS, PRODUCTS OR SERVICES DESCRIBED HEREIN. Each user bears full responsibility for making its own determination as to the suitability of Supplier's materials, services, recommendations, or advice for its own particular use. Each user must identify and perform all tests and analyses necessary to assure that its finished parts incorporating Supplier's products, materials, or services will be safe and suitable for use under end-use conditions. Nothing in this or any other document, nor any oral recommendation or advice, shall be deemed to alter, vary, supersede, or waive any provision of Supplier's standard Conditions of Sale or this Disclaimer, unless any such modification is specifically agreed to in a writing signed by Supplier. No statement contained herein concerning a possible or suggested use of any material, product, service or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Supplier covering such use or design, or as a recommendation for the use of such material, product, service or design in the infringement of any patent or other intellectual property right.

^{*}Silopren™ ist ein Markenname der Momentive Performance Materials Inc.

The use of the "TM" symbol designates registered or unregistered trademarks of Momentive Performance Materials Inc. or its affiliated companies. Momentive and the Momentive logo are trademarks of Momentive Performance Materials Inc.