

## LIM™ 6040

### Description

LIM 6040 liquid silicone rubber is a 2-component product formulated for use in liquid injection molding to high performance elastomeric parts. It is clear, but easily pigmentable with Momentive Performance Materials masterbatch colors.

### Key Features and Benefits

- High clarity for excellent visibility
- Excellent tear strength
- Convenient 1:1 mix ratio for use with automatic equipment
- Rapid cure time: 10 to 40 seconds depending upon part size, configuration, and molding temperature
- Wide range of molding temperatures: 1500C (3020F) to 2050C (4000F)
- Excellent release from metal molds

### Typical Physical Properties

<u>Uncured Properties</u>		
<u>Property</u>	<u>LIM6040 - A</u>	<u>LIM6040 - B</u>
Color	Clear, Colorless	Clear, Colorless
Specific Gravity, gm / cc	1.12	1.12
Application Rate, gm/min	66	75
<u>Mixed A &amp; B</u>		<u>LIM6040 A&amp;B</u>
Cure rate (Monsato Rheometer - MDR2000) @ 177°C (350°F)		
Max Torque, in lbs.		14
T-02, seconds		7

Peak rate, in /lb./min.	99
T-90, seconds	12

<u>Cured Properties</u>	<u>As Molded 30 sec @ 177°C (350°F)</u>	<u>Postbaked 1hr @ 204°C (400°F)</u>
Hardness, Shore A durometer	40	42
Tensile Strength, psi (MPa)	1200(8.3)	1300(9.7)
Elongation, %	650	600
Tensile Modulus @ 100%, psi (MPa)	230(1.06)	220(1.5)
Tear Strength, Die B, ppi (KN/M)	230(40.4)	230(40.4)
Compression Set, % (22hrs. @ 177C/(350F)	40	25
Bashore, %	58	54
<u>After Heat Aging 168 hr @ 177C/350F</u>		
Hardness, Shore A change	+3 pts.	+3 pts.
Tensile change	+8%	-8%
Elongation, change	1%	-15%
Tear strength, change	+5%	+5%
Bashore change	-3 pts.	+1 pt.
<u>Electrical</u>		
Dielectric Strength, V/mil	460	
Dielectric Constant @ 1000Hz	3.0	
Dissipation Factor @ 1000 Hz	0.0001	
Volume Resistivity, Ohm-cm	6.4 x 10 <sup>14</sup>	

Typical data are average data actual values may vary.

Typical data shall not be used as product specifications.

#### Potential Applications

The combination of excellent clarity, tear strength and very high tensile strength makes

this product suitable for a wide variety of applications.

- Baby bottle nipples
- Connector inserts
- Seals
- Flexible mounts
- Valves
- Sports goggles
- Masks
- Health care equipment
- Camera parts
- Coating metal rolls

### **Processing Recommendations**

Ready-to-use mixtures (of the components A and B) are fed directly to the injection-molding machine from the original containers by means of a metering and mixing unit. The mixture, consisting of the two components in the ratio 1:1, is injected into the heated mold. At mold temperatures of 170 - 230°C, the addition-crosslinking silicone rubber typically vulcanizes, without any dissociation products, within a few seconds. High curing speed and easy demolding can help enable fully automated production of a large number of articles in short cycle times.

### **Regulatory Compliance**

- A representative sample of an analogous product to LIM 6040 met the requirements of USP Class VI and ISO 10993 under Good Laboratory Practices (GLP).
- Listed as UL 94 HB (File No. E205753)
- The ingredients are listed in the BfR recommendation XV “Silicones” <sup>(1)</sup>
- Compositionally compliant with 21 CFR 177.2600 – Rubber articles intended for repeated use<sup>(2)</sup>

(1) Producer of the final article needs to test and confirm that the final product meets the extraction limits of BfR XV or corresponding EU legislation.

(2) It is the responsibility of the user to determine that the final product complies with the extractive limitations and other requirements of 21 CFR 177.2600, under their specific manufacturing procedures.

### Patent Status

Nothing contained herein shall be construed to imply the nonexistence of any relevant patents or to constitute the permission, inducement or recommendation to practice any invention covered by any patent, without authority from the owner of the patent.

### Product Safety, Handling and Storage

Customers should review the latest Safety Data Sheet (SDS) and label for product safety information, safe handling instructions, personal protective equipment if necessary, emergency service contact information, and any special storage conditions required for safety. Momentive Performance Materials (MPM) maintains an around-the-clock emergency service for its products. SDS are available at [www.momentive.com](http://www.momentive.com) or, upon request, from any MPM representative. For product storage and handling procedures to maintain the product quality within our stated specifications, please review Certificates of Analysis, which are available in the Order Center. Use of other materials in conjunction with MPM products (for example, primers) may require additional precautions. Please review and follow the safety information provided by the manufacturer of such other materials.

### Limitations

Customers must evaluate Momentive Performance Materials products and make their own determination as to fitness of use in their particular applications.

### Contact Information

Email

[commercial.services@momentive.com](mailto:commercial.services@momentive.com)

### Telephone

Americas	Latin America	EMEAI- Europe, Middle East, Africa & India	ASIA PACIFIC
+1 800 295 2392	<b>Brazil</b>	<b>Europe</b>	<b>China</b>
Toll free*	+55 11 4534 9650	+390510924300	800 820 0202
+704 805 6946	Direct Number	Direct number	Toll free

Direct Number			+86 21 3860 4892
			Direct number
*All American countries	<b>Mexico</b> +52 55 2169 7670 Direct Number	<b>India, Middle East &amp; Africa</b> + 91 44 71212207 Direct number*	<b>Japan</b> +81 3 5544 3111 Direct number
		<b>*All Middle Eastern countries, Africa, India,</b>	<b>Korea</b> +82 2 6201 4600

For literature and technical assistance, visit our website at: [www.momentive.com](http://www.momentive.com)

**DISCLAIMER:**

**THE MATERIALS, PRODUCTS AND SERVICES OF MOMENTIVE PERFORMANCE MATERIALS INC. AND ITS SUBSIDIARIES AND AFFILIATES (COLLECTIVELY “SUPPLIER”), ARE SOLD SUBJECT TO SUPPLIER’S STANDARD CONDITIONS OF SALE, WHICH ARE INCLUDED IN THE APPLICABLE DISTRIBUTOR OR OTHER SALES AGREEMENT, PRINTED ON THE BACK OF ORDER ACKNOWLEDGMENTS AND INVOICES, AND AVAILABLE UPON REQUEST. ALTHOUGH ANY INFORMATION, RECOMMENDATIONS, OR ADVICE CONTAINED HEREIN IS GIVEN IN GOOD FAITH, SUPPLIER MAKES NO WARRANTY OR GUARANTEE, EXPRESS OR IMPLIED, (i) THAT THE RESULTS DESCRIBED HEREIN WILL BE OBTAINED UNDER END-USE CONDITIONS, OR (ii) AS TO THE EFFECTIVENESS OR SAFETY OF ANY DESIGN INCORPORATING ITS PRODUCTS, MATERIALS, SERVICES, RECOMMENDATIONS OR ADVICE. EXCEPT AS PROVIDED IN SUPPLIER’S STANDARD CONDITIONS OF SALE, SUPPLIER AND ITS REPRESENTATIVES SHALL IN NO EVENT BE RESPONSIBLE FOR ANY LOSS RESULTING FROM ANY USE OF ITS MATERIALS, PRODUCTS OR SERVICES DESCRIBED HEREIN.** Each user bears full responsibility for making its own determination as to the suitability of Supplier’s materials, services, recommendations, or advice for its own particular use. Each user must identify and perform all tests and analyses necessary to assure that its finished parts incorporating Supplier’s products, materials, or services will be safe and suitable for use under end-use conditions. Nothing in this or any other document, nor any oral recommendation or advice, shall be deemed to alter, vary, supersede, or waive any provision of Supplier’s standard Conditions of Sale or this Disclaimer, unless any such

modification is specifically agreed to in a writing signed by Supplier. No statement contained herein concerning a possible or suggested use of any material, product, service or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Supplier covering such use or design, or as a recommendation for the use of such material, product, service or design in the infringement of any patent or other intellectual property right.

\*LIM™ is a trademark of Momentive Performance Materials Inc.

The use of the "™" symbol designates registered or unregistered trademarks of Momentive Performance Materials Inc. or its affiliated companies. Momentive and the Momentive logo are trademarks of Momentive Performance Materials Inc.